

## **DRTS-6**

Advanced Protection Relay Test Set and Measurement System

- Multi-tasking equipment designed for testing protection relays, energy meters, transducers
- Powerful and lightweight
- High accuracy: Better than 0.1%
- UP TO 9 CURRENT AND 4 VOLTAGE OUTPUTS PLUS AUXILIARY D.C. SUPPLY

## **APPLICATION**

DRTS-6 CAN TEST ALL THE FOLLOWING RELAYS

RELAY TYPE	IEEE No
Distance relay	21
Synchronizing device	25
Under/over-voltage relay	27/59
Directional Power relay	32
Field relay	40
Reverse phase current relay	46
Phase sequence voltage relay	47
Incomplete sequence relay	48
Instantaneous over-current rela	y 50
Inverse time over-current relay	51
Power factor relay	55
Voltage balance relay	60
Ground detector relay	64
Directional over-current relay	67
Phase angle out of step relay	78
Automatic reclosing relay	79
Frequency relay	81
Pilot wire receiver relay	85
Lockout relay	86
Differential protection relay	87
Voltage directional relay	91
Power directional relay	92
Tripping relay	94



DRTS-6 has been designed to test:

ALL PROTECTION RELAYS; WATT-HOUR METERS; TRANSDUCERS; METERS.

### **DRTS-6 SPECIFICATION**

### SIX PHASE AC/DC CURRENT OUTPUTS

### **AC/DC** CURRENT OUTPUTS

RANGE		CONNECTION	CURRENT A	POWER VA	ZMAX Ohm	RESOLUTION
1	6 X	DIRECT	015	80	0.35	230 μA
2	6 X	DIRECT	01.5		0.35	23 µA
3	6 X	DIRECT	00.15		0.35	2 µA
4	3 X	DIRECT	015	100	0.44	230 µA
5	3 X	DIRECT	01.5	,	0.44	23 µA
6	3 X	DIRECT	0 0.15		0.44	2 µA
7	3 X	2 in parallel	0 30	160	0.18	460 µA
8	3 X	2 in parallel	0 3		0.18	46 µA
9	3 X	2 in parallel	0 0.3		0.18	5 µA
10	3 X	2 in series	0 15	160	0.71	230 µA
11	2 X	3 IN PARALLEL	0 45	240	0.12	690 µA
12	1 X	6 IN PARALLEL	0 90	480	0.06	1.38 mA
13	1 X	2 IN SERIES+2 IN PARALLEL	0 30	320	0.35	460 μA

- Six independent current sources with a common neutral.
- Independent adjustment of current outputs.
- Duty cycle: continuous.
- Waveform resolution: 28 bit.
- Capable of stepping or ramping the current.
- Rate of change programmable between ± 0.001 A/s and ± 999 A/s.
- Output accuracy: ± 0.1% of the value, ± 0.02% of the range.
- Distortion: 0.1% total maximum.
- Automatic protection for overloads.

### FOUR PHASE AC/DC VOLTAGE OUTPUTS

### AC/DC VOLTAGE OUTPUTS

V VA O	hm
1 4 X DIRECT 0125 80 19	95 1.9 mV
2 3 X DIRECT 012.5 19	95 190 μV
3 3 X DIRECT 01 19	95 19 μV
4 1 X 2 IN SERIES 0250 160 39	00 3.8 mV
5 1 X 2 IN PARALLEL 0125 160 9	77 1.9 mV
OPTIONAL 300 V OUTPUT	
1 4 X DIRECT 0 300 80 112	25 4.6 mV
2 3 X DIRECT 0 125 80 19	95 1.9 mV
3 3 X DIRECT 0 12.5 19	95 190 μV
4 1 X 2 IN SERIES 0 600 160 39	90 9.2 mV
5 1 X 2 IN PARALLEL 0 300 160 9	97 <u>4.6 mV</u>

- Four independent voltage sources, with a common neutral.
- Independent adjustment of voltage outputs.
- Duty cycle: continuous.
- Waveform resolution: 28 bit.
- Capable of stepping or ramping the voltage.
- Rate of change programmable between ± 0.001 V/s and ± 999 V/s.
- $\bullet$  Voltage accuracy:  $\pm$  0.1% of the value,  $\pm$  0.02% of the range.
- Distortion: 0.1% total maximum.
- Automatic protection for overloads and counter-feed.
- The fourth voltage output can be selected to act as:

. Fourth voltage output V4 (AC/DC); . Zero-sequence component VO = (V1+V2+V3)/3 or VO = (V1 + V2 + V3/1.73).

### **BATTERY SIMULATOR**

Output voltage: 0...260 V D.C., program controlled.

Power: 50 W or 2 A on all range; continuous duty.

Accuracy: ± 1%.

Automatic protection for overloads. Step or ramp control

### **A**NGLES

Phase angle range: 0°- 360°. Angle resolution: 0.01°. Angle accuracy: ± 0.1°. Step or ramp control.

### **OUTPUT FREQUENCY**

Frequency range: from d.c. (0 Hz) to 2000 Hz. Transient 5 kHz.

Capable of generating different frequencies on any output.

Maximum frequency error:  $50 \mu Hz (1 ppm)$ .

Resolution: 0.1 mHz.

Capable of generating waveform with superimposed harmonic distortion.

### LOW LEVEL SIGNAL OUTPUTS

The purpose of these low voltage outputs is to test protection relays that use transducers such as Rogowsky coils and voltage dividers; for this simulation low voltage inputs are necessary.

Number of outputs: 6.

Full range voltage output: 0... 7.26 V rms. Full range current output: 0... 7.26 or 0...0.726 V rms.

Output current: 5 mA max. Resolution: 0.43 mV or 0.043 mV. Accuracy: 0.1% of range. Distortion: 0.1%.

### TIME MEASUREMENTS

Binary inputs: 8 inputs, clean or with voltage from 0 to 250V AC/DC, separated in two groups of 4, with two common points isolated at 1 kVac.

Selection of the type of input: Voltage clean (N.O./N.C.); 5 V; 24 V; 48 V; 110 V; software controlled.

Selection of input debounce: from 0 to 2,000 µs; software controlled.

Timer range: 0 - 999,999.9999 s (277 hours) or in cycles.

Resolution: 0.1 ms, 0.005 cycles.

Timer accuracy: 0.01% of reading  $\pm$  0.1 ms. Event recording up to 1 kHz.

### **COUNTER INPUTS**

These inputs allow testing energy meters, including high frequency outputs.

Number of inputs: 2; with no common zero point.

Frequency range: 0 to 50 kHz.

### **AUXILIARY OUTPUTS**

Four timed relay contacts; both normal open and normal closed provided.

Characteristics of contacts with a resistive load:

. Maximum voltage : 250 VAC;

. Maximum current : 5 A.

Range of programmable delay: from 0 to 999.99 s.

### **ANALOG MEASUREMENTS (OPTIONAL):**

### DC Current measuring Input, Low

. Measuring range: ± 20 mA

. Accuracy: 0.03%.

### DC Voltage measuring input, Low

. Measuring range ± 10 V.

. Accuracy: 0.03%.

### AC/DC Current measuring Input, High

. Measuring range: ± 20 A.

. Accuracy: 0.2 % D.C.; 0.3% A.C.

### AC/DC Voltage measuring input, High

. Measuring range ± 250 V

. Accuracy: 0.1% D.C.; 0.2% A.C.

### INTERFACE CONNECTION

Type of interface: RS232.

Transmission rate: 57.6 kByte/s.

### **POWER SUPPLY**

Mains power supply: 90 to 264 VAC single phase.

Frequency: 47 to 63 Hz.

Power consumption:

. at rest: less than 150 W;

. maximum load: 1600 W.

### CASE

Aluminum, with carrying handle.

### **W**EIGHT AND DIMENSIONS

Weight: 16 kg. Dimensions:

170 (h) x 470 (w) x 430 (d) mm.

# Accessories supplied with the unit

Protective carrying bag.

Power supply cable.

Serial interface cable.

Instruction and maintenance manuals.

### **ADDITIONAL EXTERNAL AMPLIFIERS FOR DRTS-6**

### **AMI-99**

THREE PHASE CURRENT AMPLIFIER

### **APPLICATION**

The three phase current amplifier AMI-99 is an additional device to the DRTS.6. DRTS-6 in connection with AMI-99 allows to have 9 currents or 6 currents at 30 A per phase or three currents at 60 A per phase.

### **AMI-99 SPECIFICATION**

AMI-99 WITH DRTS-6

RANGE		CONNECTION	CURRENT A	POWER VA	Z MAX Ohm	RESOLUTION
1	9 X	DIRECT	6 x 015	80	0.35	230 µV
			3 x 030	160	0.18	460 µV
2	9 X	DIRECT	6 x 01.5			23 µA
			3 x 03			46 µA
3	9 X	DIRECT	6 x 00.15			2.3 µA
			3 x 00.3			4.6 µA
4	6 X	DRTS-6: PARALLEL	030	160	0.18	460 µA
5	6 X	DRTS-6: PARALLEL	03		0.18	46 µA
6	6 X	DRTS-6: PARALLEL	00.3		0.18	4.6 µA
7	3 X	PARALLEL	060	320	0.09	920 µA
8	3 X	PARALLEL	06		0.09	92 µA
9	3 X	PARALLEL	00.6		0.09	9,2 µA
10	1 X	ALL IN PARALLEL	0180	760	0.023	2.8 mA

- Three independent current sources, with a common neutral.
- Automatic range switch and independent range selection.
- Waveform resolution: 28 bit.
- Output accuracy: ± 0.1% of the value, ± 0.02% of the range.
- Distortion: 0.1% total maximum, with any load
- Automatic protection for overloads.
- Angle accuracy: ± 0.1°.

### AMI-99 STAND ALONE

RANGE		CONNECTION	CURRENT A	POWER VA	Z MAX Ohm	RESOLUTION
1	3 X	DIRECT	030	160	0.18	460 µA
2	3 X	DIRECT	03		0.18	46 µA
3	3 X	DIRECT	00.3		0.18	4.6 µA
4	3 X	2 IN SERIES	030	320	0.35	460 µA
5	1 X	3 IN PARALLEL	090	480	0.06	1.38 mA

### **POWER SUPPLY**

Mains power supply: 90 to 264 V a.c., single phase.

Frequency: 47 to 63 Hz. Power consumption:

. at rest: less than 100 W; . maximum load: 1000 W.

### **WEIGHT AND DIMENSIONS**

Weight: 16 kg.

Dimensions without the handle: 170 (h) x 470 (w) x 430 (d).

### **C**ASE

Case: aluminium, with carrying handle.

# ACCESSORIES SUPPLIED WITH THE UNIT

Protective plastic bag.

Mains supply cable to DRTS.6.

Interconnecting cable to DRTS.6

### AMI-1/50:

THREE PHASE HIGH CURRENT AMPLIFIER

### **APPLICATION**

If high current or high power (or 9 current outputs) are needed for testing old electromechanical relays or for testing two secondary transformers, the DRTS-6 can control the external high current, three phase amplifier model AMI-50.



### **AMI-150 SPECIFICATION**

### AC/DC CURRENT OUTPUTS

RANGE		CONNECTION	CURRENT A	POWER VA	Z MAX Ohm	RESOLUTION
1	3 X	DIRECT	050	150	0.06	760 μA
2	3 X	DIRECT	025	150	0.24	380 μA
3	3 X	DIRECT	012.5	150	0.96	190 μΑ
4	3 X	DIRECT	02.5	150	24	38 µA
5	3 X	DIRECT	00.05	0.01	24	1 μΑ
6	1 X	3 IN SERIES	050	450	0.18	760 μA
7	1 X	3 in parallel	0150	450	0.02	2.28 mA

- Three independent current sources, without a common neutral.
- Accuracy: 0.5% of the range.
- Automatic protection for overloads.
- Waveform resolution: 24 bit.
- Frequency range: from 0 Hz to 2 kHz; transient 5 kHz.

### **Power supply**

Mains power supply: 110 or 230 Vac, single phase; to be specified at order.

Frequency: 47/63 Hz.

Power consumption, maximum load: 800 W.

### **WEIGHT AND DIMENSIONS**

Weight: 20 kg.

Dimensions: 200 (h) x 470 (w) x 380 (d).

### **C**ASE

Aluminium, with handle.

# ACCESSORIES SUPPLIED WITH THE UNIT

Power supply cable.

Connection cable to DRTS-6.

### **AMI-66**

Three phase current amplifier

### **APPLICATION**

The three phase current amplifier AMI-66 is an accessory for DRTS-6 for tests that require nine independent currents at the same time (two secondary differential transformers). The three current outputs of AMI-66 can be generated together with DRTS-6: this also allows paralleling current outputs thus increasing output current and power.

# Sales Sales

### **AMI-66 SPECIFICATION**

AMI-66 WITH DRTS-6

RANGE		CONNECTION	CURRENT A	POWER VA	Z MAX Ohm	RESOLUTION
1	3 X	DIRECT	015	80	0.35	230 μΑ
2	3 X	DIRECT	01.5		0.35	23 μΑ
3	3 X	DIRECT	00.15		0.35	2.3 μΑ
4	1 X	2 in series	015	160	0.71	230 μΑ
5	1 X	2 IN PARALLEL	030	160	0.18	460 µA

### **AMI-66** STAND ALONE

RANGE		CONNECTION	CURRENT A	POWER VA	Z MAX Ohm	RESOLUTION
1	9 X	DIRECT	015	80	0.35	230 µA
2	9 X	DIRECT	01.5		0.35	23 μΑ
3	9 X	DIRECT	00.15		0.35	2.3 µA
4	3 X	3 IN PARALLEL	045	240	0.12	690 μA
5	3 X	3 IN PARALLEL	04.5		0.12	69 μΑ
6	3 X	3 IN PARALLEL	00.45		0.12	7 μA
7	1 X	8 in parallel	0120	640	0.04	2 mA
	_					

- Three independent current sources, without a common neutral.
- Accuracy: 0.1% of the value, ± 0.02% of the range.
- Automatic protection for overloads.
- Waveform resolution: 24 bit.
- Frequency range: from 0 Hz to 2 kHz; transient 5 kHz.

### **POWER SUPPLY**

Mains power supply: 110 or 230 Vac, single phase; to be specified at order. Frequency: 47/63 Hz.

Power consumption, maximum load: 800 W.

### **WEIGHT AND DIMENSIONS**

Weight: 20 kg.

Dimensions: 200 (h) x 470 (w) x 380 (d).

### **C**ASE

Aluminium, with handle.

# ACCESSORIES SUPPLIED WITH THE UNIT

Power supply cable. Connection cable to DRTS-6.

# AMIV-66

Three phase current and voltage amplifier

### **APPLICATION**

The three phase current and voltage amplifier AMIV-66 is an accessory for the DRTS-6 for tests that require nine independent currents at the same time (two secondary differential transformers), or six voltages at the same time (synchronising devices), or six currents and six voltages. The three current outputs of AMIV-66 can be generated together with DRTS-6: this also allows paralleling current outputs, thus increasing output current and power.



### **AMIV-66 SPECIFICATION**

### THREE PHASE CURRENT GENERATOR

AMIV-66 WITH DRTS-6

RANGE		CONNECTION	CURRENT A	POWER VA	Z MAX Ohm	RESOLUTION
1	9 X	DIRECT	015	80	0.35	230 μΑ
2	9 X	DIRECT	01.5		0.35	23 μΑ
3	9 X	DIRECT	00.15		0.35	2.3 µA
4	3 X	3 IN PARALLEL	045	240	0.12	690 μA
5	3 X	3 IN PARALLEL	04.5		0.12	69 μΑ
6	3 X	3 IN PARALLEL	00.45		0.12	7 μA
7	1 X	8 IN PARALLEL	0120	640	0.04	2 mA

### AMIV-66 STAND ALONE

RANGE		CONNECTION	CURRENT A	POWER VA	Z MAX Ohm	RESOLUTION
1	3 X	DIRECT	015	80	0.35	230 μΑ
2	3 X	DIRECT	01.5		0.35	23 μΑ
3	3 X	DIRECT	00.15		0.35	2.3 μA
4	1 X	2 IN SERIES	015	160	0.71	230 µA
5	1 X	2 IN PARALLEL	030	160	0.18	460 µA

- Three independent current sources, with a common neutral.
- Output frequency: from 0 Hz to 2000 Hz; transient 5 kHz.
- Waveform resolution: 28 bit.
- Output accuracy: ± 0.1% of the value, ± 0.02% of the range.
- Distortion: 0.1% total maximum, with any load.
- Automatic protection for overloads.
- Angle accuracy: ± 0.1°.

### THREE PHASE VOLTAGE GENERATOR

AMIV/66 WITH DRTS-6

RANGE		CONNECTION	Voltage V	POWER VA	ZMAX Ohm	RESOLUTION
1	6 X	DIRECT	0125	80	195	1.9 mV
2	6 X	DIRECT	012.5		195	190 μV
3	6 X	DIRECT	01		195	19 µV
4	1 X	2 in series-par.	0250	320	195	3.8 mV
5	1 X	4 IN PARALLEL	0125	320	50	1.9 mV
		OPT	TONAL 300 V (	OUTPUT		
1	6 X	DIRECT	0 300	80	1125	4.6 mV
2	6 X	DIRECT	0 125	80	195	1.9 mV
3	6 X	DIRECT	0 12.5		195	190 μV
4	1 X	4 IN SERIES-PAR.	0 600	320	195	9.2 mV
5	1 X	4 in parallel	0 300	320	50	4.6 mV

### **AMIV/66** STAND ALONE

RANGE		CONNECTION	Voltage V	POWER VA	ZMAX Ohm	RESOLUTION
1	2 X	DIRECT	0125	80	195	1.9 mV
2	2 X	DIRECT	012.5		195	190 μV
3	2 X	DIRECT	01		195	
4	1 X	2 IN SERIES	0250	160	390	3.8 mV
5	1 X	2 IN PARALLEL	0125	160	97	1.9 mV
		OP1	FIONAL 300 V	OUTPUT		
1	2 X	DIRECT	0 300	80	1125	4.6 mV
2	2 X	DIRECT	0 125	80	195	1.9 mV
3	2 X	DIRECT	0 12.5		195	190 μV
4	1 X	2 IN SERIES	0 600	160	390	9.2 mV
5	1 X	2 IN PARALLEL	0 300	160	97	4.6 mV

- Three independent voltage sources, with a common neutral.
- Output frequency: from 0 Hz to 2000 Hz; transient 5 kHz.
- Waveform resolution: 28 bit.
- Output accuracy: ± 0.1% of the value, ± 0.02% of the range.
- Distortion: 0.1% total maximum, with any load.
- Automatic protection for overloads.
- Angle accuracy: ± 0.1°.

### **POWER SUPPLY**

Power supply voltage: 90 ... 264 Vac single phase.

Frequency: 47/63 Hz.

Power consumption, maximum load: 1000 W.

### **C**ASE

Aluminium, with carrying handle.

# ACCESSORIES SUPPLIED WITH THE UNIT

Power supply cable.

Interconnecting cable to DRTS-6.

Plastic carrying bags.

### **W**EIGHT AND DIMENSIONS

Weight: 15 kg.

Dimensions:

170 (h) x 470 (w) x 430 (d) mm.

### **AMV-66**


### TWO PHASE VOLTAGE AMPLIFIER

### APPLICATION

The two phase voltage amplifier AMV-66 is an accessory for the DRTS-6, for tests that require six voltages at the same time (synchronising devices).

### **AMV-66 SPECIFICATION**

TWO PHASE VOLTAGE GENERATOR AMV-66 WITH DRTS-6



### **AMV/66** STAND ALONE

RANGE		CONNECTION	VOLTAGE V	POWER VA	ZMAX Ohm	RESOLUTION
1	2 X	DIRECT	0125	80	195	1.9 mV
2	2 X	DIRECT	012.5		195	190 µV
3	2 X	DIRECT	0,1		195	19 µV
4	1 X	2 in series	0250	160	390	3.8 mV
5	1 X	2 IN PARALLEL	0125	160	97	1.9 mV
OPTIONAL 300 V OUTPUT						
1	2 X	DIRECT	0 300	80	1125	4.6 mV
2	2 X	DIRECT	0 125	80	195	1.9 mV
3	2 X	DIRECT	0 12.5		195	190 µV
4	1 X	2 in series	0 600	160	390	9.2 mV
5	<u>1 X</u>	2 IN PARALLEL	0 300	160	97	4.6 mV

### **OPTIONAL ACCESSORIES**

### 10-6432

DIGITAL INPUT AND OUTPUT EXPANSION

### **APPLICATION**

The option IO-6432 increases the number of logic inputs and outputs that can be monitored by the DRTS-6. The option adds to inputs and outputs that are located in the DRTS-6. The IO-6432 is fitted internally in the DRTS-6 unit.



- Three independent voltage sources, with a common neutral.
- Output frequency: from 0 Hz to 2000 Hz; transient 5 kHz.
- Waveform resolution: 28 bit.
- Output accuracy: ± 0.1% of the value, ± 0.02% of the range.
- Distortion: 0.1% total maximum, with any load.
- Automatic protection for overloads.
- Angle accuracy: ± 0.1°.

### **POWER SUPPLY**

Power supply voltage: 90 ... 264 Vac single phase.

Frequency: 47/63 Hz.

Power consumption, maximum load: 500 W.

### CASE

Aluminium, with carrying handle.

# ACCESSORIES SUPPLIED WITH THE UNIT

Power supply cable.

Interconnecting cable to DRTS-6.

### **WEIGHT AND DIMENSIONS**

Weight: 10 kg.

Dimensions:

170 (h) x 230 (w) x 430 (d) mm.

### IO-6432 SPECIFICATION

### INPUTS

Number of inputs: 64, by 4 groups of 16.

Inputs: logic, voltage from 5 to 130 V d.c.; maximum load current 3 mA.

Input and output groups are isolated from each other; they are also isolated from the rest of the instrument, from the mains supply and from the ground.

It is possible to separately program each input as Normally Open or Normally Closed or Disabled.

It is possible to separately program the timer stop of each programmed input as Trip or Reset.

Logic input time measurement resolution: 1 ms.

Logic input time measurement accuracy: 2 ms.

### OUTPUTS

Number of outputs: 32, in 4 groups of 8.

Type of outputs: open collector; maximum voltage 130 V; minimum current capability 15 mA.

It is possible to separately program each logic output as Normally Open or Normally Closed.

It is possible to separately delay each logic output with respect to currents and voltages.

Logic output time accuracy: 1 ms.

### **OPTION OUT32 FOR THE 106432 OPTION**

IO6432 outputs drive the load to zero. If the output must be driven with the voltage, or if the current is not sufficient, it is available the module OUT32, that has the following characteristics:

Inputs: 32, from IO6432 of DRTS.

Outputs: 32 relay contacts (both ends), with the following characteristics.

.Vmax: 250 V; . Imax: 0.5 A;

. Outputs protected against over-voltage;

.Time delay: less than 10 ms.

Connection to DRTS: with a cable I m long, provided.

Lights that turn on when the relay is closed.

Output connection: by two 50-way connectors.

Power supply: from the mains; 220 V 50 Hz.

Weight: 3 kg.

Dimensions: 25 x 19 x 11 cm.

Case: plastic, with graved front face.

### **OPTIONAL GPS SYNCHRONIZER**

### **APPLICATION**

External module for synchronization of two sets via GPS system, for end to end test of differential relays.

1 digital output 0-24 Vdc, for synchronisation.

1 selector to program the following pulse intervals: 5 s; 10 s; 20 s; 30 s; 40 s; 60 s.

Maximum timing error with respect to nominal: 2 µs.

Two test sets synchronized with GPS produce the maximum error of 50 µs.

Power supply: 110/220 Vac.

The option includes the antenna and connection cables.

Weight: 1.7 kg.

Dimensions: 150 x 100 x 240 mm. Case: plastic case.

### SHA-I ENERGY METERS UNIVERSAL SCANNING HEAD

### **APPLICATION**

SHA-1 is a scanning head that eases the test of energy meters. It is an universal scanning head because it can be used both with LED impulse electronic meters and Ferraris rotating disk meters. With rotating disk the sensor uses a green light beam that optimizes the recognition of any type of mark.

With LED recognition the following specification applies:

- . Impulse duration: more than 60 us;
- . Impulse frequency: less than 500 Hz;
- . Duty cycle: 50%;
- . Light wavelength: 500 to 960 nm (red).

The option includes:

- . A support to keep the scanning head in front of the energy meter;
- .The cable, 2 m long, from the scanning head to the DRTS-6;
- . The power supply transformer, for the power of 220 Vac, to supply the scanning head.

### **APPLICABLE STANDARDS**

### **ELECTROMAGNETIC COMPATIBILITY**

Directive no. 89/336/CEE dated May 3, 1989, modified by the directive 92/31/CEE dated May 5, 1992. Applicable Standards: EN 50081-2; EN 50082-2; EN 55011; EN 61000-3-3; EN 50082-2; ENV 50140; ENV 50141; ENV 50204; IEC 1000-4-2; IEC 1000-4-4; IEC 1000-4-6; IEC 1000-4-8.

### LOW VOLTAGE DIRECTIVE

Directive n. 73/23/CEE, modified by the directive 93/68/CEE.

Applicable standards, for a class I instrument, pollution degree 2, Installation category II:
CEI EN 61010-1.
In particular:
Operating temperature: 0 - 45°C; storage: - 25°C to 70°C.
Relative humidity:
10 - 80% without condensing.

ISA SRL VIA BERGAMO, 35 21020 TAINO (VA) ITALY TEL. + 39 0331 956.081 FAX + 39 0331 957.091 Web site: www.isatest.com

E-Mail: isa@isatest.com

